

# LOFTOP™ Nylon filter cartridges

Eaton's LOFTOP
Nylon filter cartridges
are suitable for the
filtration of solvents,
amine, glycol solutions,
hydrocarbon
(kerosene), solvent and
aqueous based paints,
lacquers, emulsions,
waxes, return
condensate and high
temperature fluids.

LOFTOP Nylon filter cartridges are made of high purity polyamide 6.6 fibers. The product includes an integral fiberglass reinforced polyamide support core with optional stainless steel core available.

### **Features and benefits**

- Made of high purity polyamide 6.6 fibers (melt blown)
- No binders or adhesives
- Excellent chemical and thermal compatibility
- Available in a variety of end cap/adapter configurations to fit all industry-standard housings
- Beta rating of 5000, 99.98% efficiency
- Individually sealed in plastic foil

### Design

### Filter material Polyamide 6.6 (melt blown)

Inner core
Polyamide 6.6 fiberglass

## reinforced End caps

Polyamide 6.6

### **O**-rings

Silicone (standard), Buna-N, EPDM, fluorelastomer, FEP encapsulated

### **Retention ratings**

0.5, 1, 3, 5, 10, 20, 50, 120 μm @ 99.98% efficiency

### **Technical data**

### Nominal lengths

9.75", 10", 20", 29.25", 30", 40" (247, 254, 508, 743, 762, 1016 mm)

### **Outside diameter**

2.5" (63 mm)

### Inside diameter 1.1" (27 mm)

# Max. operating temperature 302°F (150°C)

### Max. differential pressures\*

90 psid @ 86°F (6.2 bar @ 30°C) 80 psid @ 158°F (5.5 bar @ 70°C) 70 psid @ 212°F (4.8 bar @ 100°C) 50 psid @ 302°F (3.4 bar @ 150°C)

\* Only fiberglass reinforced polyamide 6.6 inner core

# Recommended differential change-out pressure for disposal


35 psid (2.4 bar)



### LOFTOP nylon filter cartridges


### Flow rate\*

(70 °F/21 °C per 10" filter cartridge for water)



<sup>\*</sup> For liquids other than water, multiply pressure drop by fluid viscosity in centipoise.

### **Ordering code**



### North America

44 Apple Street Tinton Falls, NJ 07724 Toll Free: 800 656-3344 (North America only) Tel: +1 732 212-4700

### Furone/Africa/Middle East Auf der Heide 2

53947 Nettersheim, Germany Tel: +49 2486 809-0

Friedensstraße 41 68804 Altlußheim, Germany Tel: +49 6205 2094-0

An den Nahewiesen 24 55450 Langenlonsheim, Germany Tel: +49 6704 204-0

No. 3, Lane 280, Linhong Road Changning District, 200335 Shanghai, P.R. China Tel: +86 21 5200-0099

100G Pasir Panjang Road #07-08 Singapore 118523 Tel: +65 6825-1668

Bua Clark 2061 - Macuco 13279-400 - Valinhos, Brazil Tel: +55 11 3616-8400

### For more information, please email us at filtration@eaton.com or visit www.eaton.com/filtration

© 2018 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommenda-tions appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

EF-LTN 05-2018



